

## Dosing venturis for hygiene machines

Under the effect of the water pressure, the Venturi dispenser drives and dilutes one or two liquid products intended to clean hands or equipment contaminated by their use.

## Utilisations

- Dishwasher tunnels
- Hand disinfection
- Boot washer

## Characteristics of BC20110 and BC20111

Venturi for product suction. Automatic control

- 1 venturi 3.5 mm blue insert for the BC20110 or 1 green 2.8 mm venturi for the BC20111
- 1 easily removable non-return valve, ceramic ball, Hastelloy® spring and EPDM O-ring
- 1 flexible of 1.20m
- 1 strainer with ballast
- 1 set of dilution nozzle

BC20110 et BC20111



## Characteristics of BC20120

Venturi for aspiration of 2 products. Automatic control.

- 1 venturi 3.5 mm blue insert
- 2 easily removable non-return valves, ceramic ball, Hastelloy® spring and EPDM O-ring
- 2 hoses of 1.20m
- 2 strainers with ballast
- 2 sets of dilution nozzles

BC20120



## Characteristics of BC30110

Venturi for product suction. Automatic control

- 1 venturi 3.5 mm blue insert
- 1 easily removable non-return valve, ceramic ball, Hastelloy® spring and EPDM O-ring
- 1 flexible of 1.20m
- 1 strainer with ballast
- 1 set of 15 dilution nozzle (0,2% à 16%)

BC30110



## Characteristics of BC30120

Venturi for aspiration of 2 products. Automatic control.

- 1 manual key
- 1 venturi 3.5 mm green insert
- 2 easily removable non-return valves, ceramic ball, Hastelloy® spring and EPDM O-ring
- 2 hoses of 1.20m
- 2 strainers with ballast
- 2 sets of dilution nozzles

BC30120

